

GA 18 LTX (600638840) Cordless Die Grinder
18V ; MetaLoc

Order no. 600638840
EAN 4007430287250



Product may differ from Image



- Spindle lock for simple change of tools
- Restart protection: prevents unintentional start-up after battery pack change
- Overload protection: protects the motor from overheating
- Removable protective rubber cap for comfortable and safe working
- Slim design for ideal handling
- Precision collet for precise concentricity
- Battery packs with capacity display for checking the charge status
- Ultra-M technology: highest performance, gentle charging and 3 years of warranty on the battery pack.

Technical data

Characteristics

Battery voltage	18 V
No-load speed	25000 rpm
Collar diameter	43 mm / 1 11/16 "
Collet chuck bore	6 mm / 0.2362 "
Weight (including battery pack)	2.1 kg / 4.6 lbs

Vibration

Surface grinding (up to Ø 25 mm)	5.3 m/s ²
Surface grinding (up to Ø 50 mm)	13.9 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	83 dB(A)
Sound power level (LwA)	94 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Collet 6 mm
Open-jawed spanner
MetaLoc case
without battery pack, without charger
Protective rubber cap
Dust protection filter