



Electric Components > Products > Circular connectors > M23 Signal > M23 Signal housing > M23 Signal panel connector > [M23 Signal panel connector](#)

7.486.500.00S M23 Signal panel connector

Cable diameter	7 – 12 mm
Installation type	Strain relief
Locking type	Snap in
Material housing	brass, Die Casting
Material housing surface	Nickel
Material seals/o-rings	NBR
Version	TWILOCK-S
Wall thickness	max. 8 mm
Wrench size 1	24 mm
Wrench size 2	24 mm
Panel hole	Ø 25 + 0,1 mm

- // Housing without contact inserts
- // Electrical data depend on the contact insert
- // Pluggable with Speedtec
- // [M23 Signal Inserts](#)
- // [M23 Signal Contacts](#)
- // [M23 Signal Accessories](#)
- // You can find further information in the [Technology Center](#)

Additional information

- // [Assembly instruction M23 Signal panel connector pin](#)
- // [Assembly instruction M23 Signal panel connector socket](#)
- // [Note on storage of articles with elastomer components](#)

