

MILAN S.r.l. a socio unico

Head Office – Export department:

Viale Europa, 74
20090 Cusago (MI) Italy
T. +39 02 9039.4556-4158
F. +39 02 9039.4551
www.taskercables.com

Ufficio Commerciale e Centro Distribuzione

Viale Europa 72 Strada F12
20090 Cusago (MI) Italy
T. +39 02 9039.0037-0059
F. +39 02 9039.0049
www.tasker.it

FirestoP®

Technical Datasheet

tasker® TSK 1172 - 2x0,50 mm²

Alimentation Cable for LED

✓
RoHS
2002/95/EC
2011/65/UE



CATEGORY Cable for Led (See Electronics Catalogue)
APPLICATIONS Electronics and LED alimentation

- A:** White Soft **Flame Retardant PVC** Sheath.
Outer cable Diam. Ø 5,80 (±0,20) mm.
- B:** The cores are stranded in a pair with waste filler between conductors and wrapped with not woven polyester based tape.
Insulation with PVC, colored one Black and one Red.
Core Diam. Ø 2,00 (±0,20) mm.
- C:** O.F.C. red copper stranded formation 16x0.20 mm.
Nom. Cross section 2x0,50 mm².

MARKING **tasker®** LED CABLE RGB O.F.C. FirestoP® - Made in Italy
CUSTOM This product may be custom produced also in **LSZH, PE, PUR,**
PRODUCTION with or without Metallic Armor.

Properties

Conductor Resistance	38,00 Ω/Km
Rating Voltage	49 V
Operative Temperature	-20/+70°C

USE	X	Indoor	Interno Edificio
Impiego	X	Outdoor Limited	Esterno Limitato
		Outdoor	Esterno
		Outdoor Direct Burial	Esterno Interrato

INSTALLATION	X	Fixed	Fissa
Posa	X	Restricted Mobile	Mobile Limitata
		Mobile	Mobile
		Mobile in Drag Chain	Mobile in Catena

INFORMATION	X	RoHS2 Compliant
Informazioni	X	Ver. A / 26.05.17