

Technical Datasheet **FirestoP®** **RoHS₃** **tasker® TSK 1174 – 3x0,35+1x0,50 mm²** **O.F.C Led Cable + Power**



CATEGORY RGB Cable (See Electronics Catalogue)
APPLICATIONS Led alimentations and electronics.

A: White Soft **Flame Retardant PVC**. Outer cable Diam. Ø 5,50 (±0,20) mm.
B: The cores are stranded in a pair with waste filler between conductors and wrapped with not woven polyester based tape.

RGB Section

C: The three conductors are insulated with PVC, colored Red, Green and Blue. Diam. Ø 1,80 (±0,20) mm.

D: O.F.C. red copper formation 11x0,20 mm. Nom. Cross section 3x0,35 mm²

Power Section

E: The conductor is insulated with PVC, color Black. Diam. Ø 2,00 (±0,20) mm.

F: O.F.C. red copper formation 16x0,20 mm. Nom. Cross section 1x0,50 mm²

MARKING **tasker®** Led Cable – RGB - FirestoP® - Made In Italy
CUSTOM This product may be custom produced also in L.S.Z.H. polymer, PE, PUR,
PRODUCTION with or without Metallic Armor.

RGB Properties

Conductor Resistance	58 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-20/+70°C

Power Properties

Conductor Resistance	38 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-20/+70°C

USE	X	Indoor	Interno Edificio
Impiego	X	Outdoor Limited	Esterno Limitato
		Outdoor	Esterno
		Outdoor Direct Burial	Esterno Interrato

INSTALLATION	X	Fixed	Fissa
Posa	X	Restricted Mobile	Mobile Limitata
		Mobile	Mobile
		Mobile in Drag Chain	Mobile in Catena

INFORMATION	X	RoHS2 Compliant
Informazioni	X	Ver. A / 16.05.16