


Seal Ring

PANEL CUTOUT
MAX.PANEL THICKNESS
6 mm

Contact Composition

Operation Position	Switch Type	45° three position	
		2NO2NC	
		Left contacts: NO, NC Right contacts: NO, NC	
		Left contacts: NO, NC Right contacts: NO, NC	
		Left contacts: NO, NC Right contacts: NO, NC	

Part Number: LAS1-AF-□X/◇◆/△/◎

□	Contact structure
22	2NO 2NC

◇	Operation position
3	Three Position

◆	Operation type
1	Maintain
3	Return

△	Cap Color
R	Red
G	Green
Y	Yellow

◎	IP class
No Letter	IP40
P	IP65

SPECIFICATIONS:

- Switch Rating: AC220V/0.5A, DC110V/0.1A.
- Mechanical Life: $\geq 200,000$ cycles.
- Electrical Life: $\geq 50,000$ cycles.
- Contact Resistance: $\leq 50\text{m}\Omega$.
- Insulation Resistance: $\geq 100\text{M}\Omega$.
- Dielectric Strength:
Between terminals of the same pole: AC 1,500V, RMS 50Hz, 1min;
Between terminals of different pole: AC 2,000V, RMS 50Hz, 1min.
- Operating Temperature: $-25^{\circ}\text{C} \sim +55^{\circ}\text{C}$ (No Freezing).
- IP Class: IP40, IP65 (Maintain can made to order).
- Terminal Type: Pin Terminal (2.8 x 0.5mm).

MATERIALS:

- Contact: Silver alloy.
- Head: PC.
- Body: PC.
- Base: PBT.

BRAND 品牌 ONPOW		红波按钮制造有限公司 ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ONPOW PUSH BUTTON MANUFACTURE CO.,LTD. AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.		USED 用途	APPD 审核 CH 2019/06/10
		FINISH 处理	CHKD 校对 NCH 2019/06/10
		SCALE 比例 1.4 : 1	UNIT 单位 mm
		DR. 制图 ZPD 2019/06/10	
DIMENSIONS		TOLERANCE	
0.00 TO 18.00mm		±0.43mm	
18.01 TO 30.00mm		±0.52mm	
30.01 TO 50.00mm		±0.62mm	
50.01 TO 80.00mm		±0.74mm	
TITLE 名称 LAS1-A Series selector switch			
DWG NO. 图号 LAS1-AF-X三位置		SIZE 图纸 A4	
FILE NAME 档案名称 LAS1-A-X.DWG		SHEET 张 1 / 1	REV. 更改 1