


FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人



PANEL CUTOUT
MAX.PANEL THICKNESS
6 mm

Contact Composition

Operation Position Switch Type		90° Two Position			
		1NO1NC		2NO2NC	
 	NO NC C	NO NC C	NO NC C	NO NC C	
	Left C	Right C	Left C	Right C	

"□"	Contact structure
11	1NO 1NC
22	2NO 2NC

	Operation position
2	Two Position
	Operation type
1	Maintain
3	Return

"△"	Cap Color
R	Red
G	Green
Y	Yellow

" "	IP class
No Letter	IP40
P	IP65

Part Number: LAS1-AF-□X/◇◆/△/◎

SPECIFICATIONS:

- 1.Switch Rating: AC220V/0.5A, DC110V/0.1A.
- 2.Mechanical Life: $\geq 200,000$ cycles.
- 3.Electrical Life: $\geq 50,000$ cycles.
- 4.Contact Resistance: $\leq 50\text{m}\Omega$.
- 5.Insulation Resistance: $\geq 100\text{M}\Omega$.
- 6.Dielectric Strength:
Between terminals of the same pole: AC 1,500V, RMS 50Hz, 1min;
Between terminals of different pole: AC 2,000V, RMS 50Hz, 1min.
- 7.Operating Temperature: $-25^{\circ}\text{C} \sim +55^{\circ}\text{C}$ (No Freezing).
- 8.IP Class: IP40,IP65(Maintain can made to order).
- 9.Terminal Type: Pin Terminal(2.8 x 0.5mm).

MATERIALS:

- 1.Contact: Silver alloy.
- 2.Head: PC.
- 3.Body: PC.
- 4.Base: PBT.

BRAND 品牌						红波按钮制造有限公司 ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ONPOW PUSH BUTTON MANUFACTURE CO.,LTD. AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.		USED 用途		APPD 审核		CH		2019/06/10	
		FINISH 处理		CHKD 校对		NCH		2019/06/10	
		SCALE 比例		1.4 : 1		UNIT 单位		mm	
				DR. 制图		ZPD		2019/06/10	
DIMENSIONS 0.00 TO 18.00mm 18.01 TO 30.00mm 30.01 TO 50.00mm 50.01 TO 80.00mm		TOLERANCE ±0.43mm ±0.52mm ±0.62mm ±0.74mm		TITLE 名称 LAS1-A Series selector switch					
		DWG NO. 图号		LAS1-AF-X二位置				SIZE 图纸 A4	
		FILE NAME 档案名称 LAS1-A-X.DWG				SHEET 张		1 / 1	
						REV. 更改		1	