

1	2	3	4	5	6	7																																										
				FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人																																										
10 2.5 3 1NO1NC in this way 6 Max. Ø16 15.5 22 8 M16 x 1 Ø18				Ø16^{+0.2}₀ 14.8^{+0.2}₀ 0.6 Ø17 Ø15 Seal Ring																																												
				PANEL CUTOUT MAX.PANEL THICKNESS 6 mm																																												
Contact Composition				Part Number:LAS1-AY-□X/◇◆/△/◎																																												
<table><tr><th>Operation Position \ Switch Type</th><th colspan="2">90° Two Position</th></tr><tr><th></th><th>1NO1NC</th><th>2NO2NC</th></tr><tr><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td></tr></table>				Operation Position \ Switch Type	90° Two Position			1NO1NC	2NO2NC							<table><tr><th>□</th><th>Contact structure</th></tr><tr><td>11</td><td>1NO 1NC</td></tr><tr><td>22</td><td>2NO 2NC</td></tr></table> <table><tr><th>◇</th><th>Operation position</th></tr><tr><td>2</td><td>Two Position </td></tr></table> <table><tr><th>◆</th><th>Operation type</th></tr><tr><td>1</td><td>Maintain </td></tr><tr><td>3</td><td>Return </td></tr></table> <table><tr><th>△</th><th>Cap Color</th></tr><tr><td>R</td><td>Red</td></tr><tr><td>G</td><td>Green</td></tr><tr><td>Y</td><td>Yellow</td></tr></table> <table><tr><th>◎</th><th>IP class</th></tr><tr><td>No Letter</td><td>IP40</td></tr><tr><td>P</td><td>IP65</td></tr></table>			□	Contact structure	11	1NO 1NC	22	2NO 2NC	◇	Operation position	2	Two Position	◆	Operation type	1	Maintain	3	Return	△	Cap Color	R	Red	G	Green	Y	Yellow	◎	IP class	No Letter	IP40	P	IP65
Operation Position \ Switch Type	90° Two Position																																															
	1NO1NC	2NO2NC																																														
□	Contact structure																																															
11	1NO 1NC																																															
22	2NO 2NC																																															
◇	Operation position																																															
2	Two Position																																															
◆	Operation type																																															
1	Maintain																																															
3	Return																																															
△	Cap Color																																															
R	Red																																															
G	Green																																															
Y	Yellow																																															
◎	IP class																																															
No Letter	IP40																																															
P	IP65																																															
SPECIFICATIONS:				MATERIALS:																																												
1.Switch Rating: AC220V/0.5A, DC110V/0.1A.				1.Contact: Silver alloy.																																												
2.Mechanical Life: ≥200,000cycles.				2.Head: PC.																																												
3.Electrical Life: ≥50,000cycles.				3.Body: PC.																																												
4.Contact Resistance: ≤50mΩ.				4.Base: PBT.																																												
5.Insulation Resistance: ≥100MΩ.																																																
6.Dielectric Strength:																																																
Between terminals of the same pole: AC 1,500V, RMS 50Hz, 1min;																																																
Between terminals of different pole: AC 2,000V, RMS 50Hz, 1min.																																																
7.Operating Temperature: -25℃～+55℃(No Freezing).																																																
8.IP Class: IP40,IP65(Maintain can made to order).																																																
9.Terminal Type: Pin Terminal(2.8 x 0.5mm).																																																
				BRAND 品牌 ONPOW																																												
				红波按钮制造有限公司 ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.																																												
				USED 用途		APPD 审核 CH 2019/06/10																																										
				FINISH 处理		CHKD 校对 NCH 2019/06/10																																										
				SCALE 比例 1.4 : 1		UNIT 单位 mm																																										
				DR. 制图 ZPD 2019/06/10																																												
				TITLE 名称 LAS1-A Series selector switch																																												
				DWG NO. 图号 LAS1-AY-X二位置		SIZE 图纸 A4																																										
				FILE NAME 档案名称 LAS1-A-X.DWG		SHEET 张 1 / 1																																										
				REV. 更改 1																																												
1	2	3	4	5	6	7																																										