





PANEL CUTOUT
MAX.PANEL THICKNESS
6 mm

Contact Composition



Part Number:LAS1-AJ-□X/◇◆/△/▲/◎

"□"	Contact structure
22	2NO 2NC
"◇"	Operation position
3	Three Position
"◆"	Operation type
1	Maintain
3	Return

"△"	Lamp Color
R	Red
G	Green
Y	Yellow

"▲"	Lamp Voltage
6V	AC/DC 6V
12V	AC/DC 12V
24V	AC/DC 24V
110V	AC/DC 110V
220V	AC/DC 220V
Other voltage can be made to order	

"◎"	IP class
No Letter	IP40
P	IP65

SPECIFICATIONS:

- 1.Switch Rating: AC220V/0.5A, DC110V/0.1A.
- 2.Mechanical Life: ≥200,000cycles.
- 3.Electrical Life: ≥50,000cycles.
- 4.Contact Resistance: ≤50mΩ.
- 5.Insulation Resistance: ≥100MΩ.
- 6.Dielectric Strength:
Between contact and lamp terminals: AC 2,000V, RMS 50Hz, 1min;
Between terminals of the same pole: AC 1,500V, RMS 50Hz, 1min;
Between terminals of different pole: AC 2,000V, RMS 50Hz, 1min.
- 7.Operating Temperature: -25℃~ +55℃(No Freezing).
- 8.IP Class: IP40,IP65(Maintain can made to order).
- 9.Terminal Type: Pin Terminal(2.8 x 0.5mm).

MATERIALS:

- 1.Contact: Silver alloy.
- 2.Head: PC.
- 3.Body: PC.
- 4.Base: PBT.

BRAND 品牌 ONPOW		红波按钮制造有限公司 ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ONPOW PUSH BUTTON MANUFACTURE CO.,LTD. AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.		USED 用途	APPD 审核 CH 2020/04/26
		FINISH 处理	CHKD 校对 NCH 2020/04/26
		SCALE 比例 1.4 : 1	UNIT 单位 mm
		DR. 制图 ZPD 2020/04/26	
		TITLE 名称 LAS1-A Series selector switch	
		DWG NO. 图号 LAS1-AJ-X三位带灯	SIZE 图纸 A4
		FILE NAME 档案名称 LAS1-A-X.DWG	SHEET 张 1 / 1
			REV. 更改 1