


KEMET Part Number: SMP253MA4390MTR24
(P101AA392M250V, SMP253MA4390MT1)

SMP253/P101, Film, Metallized Paper, Safety, 3900 pF, 20%, 250 VAC, 250 VDC, 100°C, 5045, 6.5mm



Note: '()' correspond to the letters used in the product bulletin

Dimensions	
Chip Size	5045
L	12.7mm +/-0.2mm
W	11.5mm +/-0.2mm
T	6.5mm +/-0.2mm
F	0.5mm NOM

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	600

General Information	
Series:	SMP253/P101
Dielectric:	Metallized Paper
Style:	SMD Chip
RoHS:	Yes

Specifications	
Capacitance:	3900 pF
Capacitance Tolerance:	20%
Voltage AC:	250 VAC
Voltage DC:	250 VDC
Temperature Range:	-40/+100°C
Rated Temperature:	100°C
Dissipation Factor:	1.3% 1kHz
Insulation Resistance:	12 GOhms
Max dV/dt:	2000 V/us
Safety Class:	Y2