



BN 84403

Hexalobular (6 Lobe) socket pan head screws «Freedriv»

with uncontinuous slot

Steel case-hardened

zinc plated blue



ISO 4042

Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!
Further notice to residual risks can be found in the introduction section.

Article#	ø nominal	d ₁	d ₂ max.	k max.	n max.		A~	t min.	t max.	L
8278024	2,2	2,2	4	1,6	0,65	X6	1,75	0,6	0,8	6
8278032										8
8278040										10
8278059										12
8278067	2,5	2,5	5	2,1	0,8	X8	2,4	0,83	1,13	6
8278075										8
8278083										10
8278091										12
8278105										14
8278113										16
8278121	3	3	5,6	2,4	1	X10	2,8	0,96	1,26	8
8278148										10
8278156										12
8278164										14
8278172										16
8278180										20
8278199	4	4	8	3,1	1,51	X20	3,95	1,3	1,6	10
8278202										12
8278210										14
8278229										16
8278237										20
8278245										25
8278253	5	5	9,5	3,7	1,51	X25	5	1,5	1,9	12
8278261										14
8278288										16
8278296										20
8278318										25