




Notes:
1.RoHS Compliant;
2.Top Hole:Ø4.75±0.08mm,
Panel Thickness:0.79-1.98mm;
3.Bottom Hole:Ø4.0±0.08;
Panel Thickness:1.57mm;

Part No.	Article No.	Part No.	Article No.	A
40346	8G813V40346	41462	8GG01V41462	4.8 ⁺⁰ _{-0.55}
40347	8G813V40347	41463	8GG01V41463	6.4
40348	8G813V40348	41464	8GG01V41464	7.9
40349	8G813V40349	40350	8GG01V40350	9.5
40351	8G813V40351	41465	8GG01V41465	11.1
40352	8G813V40352	41466	8GG01V41466	12.7
40353	8G813V40353	41467	8GG01V41467	15.9
40354	8G813V40354	41468	8GG01V41468	19.1
40355	8G813V40355	41469	8GG01V41469	22.2
40356	8G813V40356	41470	8GG01V41470	25.4
40357	8G813V40357	41471	8GG01V41471	28.6
40358	8G813V40358	41472	8GG01V41472	31.7
40359	8G813V40359	41473	8GG01V41473	34.9

			Part No.	Article No.	Part No.	Article No.	A
			42056	8G813V42056	42289	8GG01V42289	6.0
Part No.	Article No.	A	40764	8G813V40764	42293	8GG01V42293	8.0
40039	8GG01V40039	19.1	42058	8G813V42058	42290	8GG01V42290	10.0
40040	8GG01V40040	22.2	42059	8G813V42059	42291	8GG01V42291	12.0
40041	8GG01V40041	25.4	42060	8G813V42060	42292	8GG01V42292	14.0
40042	8GG01V40042	28.6	41288	8G813V41288	42294	8GG01V42294	16.0
Material: PEI UL94 V0 Color:Black			Material: PA66 UL94 V2 Color: Natural		Material: PA66 UL94 V0 Color: Natural		

DREMEC Befestigungselemente GmbH						DATE	2020-02-28	DIMENSION	TOLERANCE
TITLE	LOCKING CIRCUIT BOARD SUPPORT					SCALE	FIT	L≤4	±0.10
ARTICLE NO.	8GG01V40039	MOLD NO.	S0315/348	DRAW	JF	UNIT	MM	4<L≤15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	JF	VERSION	A0	15<L≤50	±0.30
DWG NO.	E4022	COLOR	SEE TABLE	APPROVAL	FDL	VIEW		50<L≤100	±0.40