





Notes:

- 1.Color:Natural;
- 2.RoHS Compliant;
- 3.Top Hole:Ø4.75±0.08mm,
Panel Thickness:0.79-1.98mm;
- 4.Bottom Hole:Ø4.0±0.08;
Panel Thickness:1.57mm;

Part No.	Part Name	Part No.	Part Name	A
42533		42675	8G820V42675	6.0
42534		42676	8G820V42676	8.0
42535		42677	8G820V42677	10.0
42536		42678	8G820V42678	12.0
42537		42679	8G820V42679	14.0
42538		42680	8G820V42680	16.0
Material: PA66 UL94 V2		Material: PA66 UL94 V0		

Part No.	Part Name	Part No.	Part Name	A
40374	8G813V40374	42663	8G820V42663	4.8 ⁺⁰ _{-0.55}
40375	8G813V40375	40376	8G820V40376	6.4
40377	8G813V40377	42664	8G820V42664	7.9
40378	8G813V40378	42665	8G820V42665	9.5
40379	8G813V40379	42666	8G820V42666	11.1
40380	8G813V40380	42667	8G820V42667	12.7
40381	8G813V40381	42668	8G820V42668	15.9
40382	8G813V40382	42669	8G820V42669	19.1
40383	8G813V40383	42670	8G820V42670	22.2
40384	8G813V40384	42671	8G820V42671	25.4
40385	8G813V40385	42672	8G820V42672	28.6
40386	8G813V40386	42673	8G820V42673	31.7
40387	8G813V40387	42674	8G820V42674	34.9
Material: PA66 UL94 V2		Material: PA66 UL94 V0		

DREMEC Befestigungselemente GmbH						DATE	2020.02.28	DIMENSION	TOLERANCE
TITLE	LOCKING CIRCUIT BOARD SUPPORT					SCALE	FIT	L≤4	±0.10
PART NAME	8G813V40374	MOLD NO.	S0315/348	DRAW	PLK	UNIT	MM	4<L≤15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	15<L≤50	±0.30
DWG NO.	E4024	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		50<L≤100	±0.40