




Notes:

- 1.Color: Natural;
- 2.RoHS Compliant;
- 3.Top Hole: Ø3.18±0.05mm,
Panel Thickness: 0.79-1.98mm;
- 4.Bottom Hole: Ø3.18±0.05mm,
Panel Thickness: 1.57mm.

Part No.	Part Name	Part No.	Part Name	A
40850	8G813V40850	40851	8G813V40851	3.2
40852	8G813V40852	40853	8G813V40853	4.8
40854	8G813V40854	40855	8G813V40855	6.4
40856	8G813V40856	40857	8G813V40857	7.9
40858	8G813V40858	40859	8G813V40859	9.5
40860	8G813V40860	40861	8G813V40861	11.1
40862	8G813V40862	40863	8G813V40863	12.7
42123	8G813V42123	42127	8G820V42127	14.3
40864	8G813V40864	40865	8G813V40865	15.9
Material: PA66 UL94 V2		Material: PA66 UL94 V0		

DREMEC Befestigungselemente GmbH						DATE	2020.02.29	DIMENSION	TOLERANCE
TITLE	LOCKING CIRCUIT BOARD SUPPORT					SCALE	FIT	L≤4	±0.10
PART NAME	8G813V40850	MOLD NO.	S0390	DRAW	PLK	UNIT	MM	4<L≤15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	15<L≤50	±0.30
DWG NO.	E4075	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		50<L≤100	±0.40