





Notes:

- 1.Color:Natural;
- 2.RoHS Compliant;
- 3.Top Hole: Ø4.0±0.08mm,  
Panel Thickness: 1.6mm;
- 4.Bottom Hole: Ø4.8±0.08mm,  
Panel Thickness: 1.6mm.

| Part No.               | Part Name   | Part No.               | Part Name   | A    |
|------------------------|-------------|------------------------|-------------|------|
| 40410                  | 8G817V40410 | 41967                  | 8G817V41967 | 3.0  |
| 40411                  | 8G817V40411 | 41968                  | 8G817V41968 | 4.0  |
| 40412                  | 8G817V40412 | 41969                  | 8G817V41969 | 6.0  |
| 40413                  | 8G817V40413 | 41970                  | 8G817V41970 | 8.0  |
| 40414                  | 8G817V40414 | 41971                  | 8G817V41971 | 10.0 |
| 40415                  | 8G817V40415 | 41972                  | 8G817V41972 | 12.0 |
| 40416                  | 8G817V40416 | 41973                  | 8G817V41973 | 14.0 |
| 40417                  | 8G817V40417 | 41974                  | 8G817V41974 | 16.0 |
| 40418                  | 8G817V40418 | 41975                  | 8G817V41975 | 18.0 |
| Material: PA66 UL94 V2 |             | Material: PA66 UL94 V0 |             |      |

|                                  |                                    |          |           |          |     |         |                                                                                       |           |           |
|----------------------------------|------------------------------------|----------|-----------|----------|-----|---------|---------------------------------------------------------------------------------------|-----------|-----------|
| DREMEC Befestigungselemente GmbH |                                    |          |           |          |     | DATE    | 2020.03.03                                                                            | DIMENSION | TOLERANCE |
| TITLE                            | DUAL LOCKING CIRCUIT BOARD SUPPORT |          |           |          |     | SCALE   | FIT                                                                                   | L≤4       | ±0.10     |
| PART NAME                        | 8G817V40410                        | MOLD NO. | S0316/49  | DRAW     | PLK | UNIT    | MM                                                                                    | 4<L≤15    | ±0.20     |
| PART NO.                         | SEE TABLE                          | MATERIAL | SEE TABLE | DESIGN   | PLK | VERSION | A0                                                                                    | 15<L≤50   | ±0.30     |
| DWG NO.                          | E4027                              | COLOR    | SEE NOTES | APPROVAL | FDL | VIEW    |  | 50<L≤100  | ±0.40     |