





Part No.	Part Name	Part No.	Part Name	Part No.	Part Name	A
40800	8G817V40800	40798	8G817V40798	41983	8G817V41983	4.8
40801	8G817V40801	43126	8G817V43126	41984	8G817V41984	6.4
40802	8G817V40802	43127	8G817V43127	41985	8G817V41985	7.9
40803	8G817V40803	43128	8G817V43128	41986	8G817V41986	9.5
40804	8G817V40804	43129	8G817V43129	41987	8G817V41987	11.1
40805	8G817V40805	43130	8G817V43130	41988	8G817V41988	12.7
40806	8G817V40806	43131	8G817V43131	41989	8G817V41989	14.3
40807	8G817V40807	43132	8G817V43132	41990	8G817V41990	15.9
40799	8G817V40799	43133	8G817V43133	40876	8G817V40876	22.2
Material: PA66 UL94 V2 Color: Natural		Material: PA66 UL94 V2 Color: Black		Material: PA66 UL94 V0 Color: Natural		

Notes:

- 1.RoHS Compliant;
- 2.Top Hole: Ø3.18±0.05mm,
Panel Thickness: 0.79-1.98mm;
- 3.Bottom Hole: Ø3.18±0.05mm,
Panel Thickness: 0.79-1.98mm.

DREMEC Befestigungselemente GmbH						DATE	2020.03.03	DIMENSION	TOLERANCE
TITLE	DUAL LOCKING CIRCUIT BOARD SUPPORT					SCALE	FIT	L≤4	±0.10
PART NAME	8G817V40800	MOLD NO.	S0390	DRAW	PLK	UNIT	MM	4 < L ≤ 15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	15 < L ≤ 50	±0.30
DWG NO.	E4070	COLOR	SEE TABLE	APPROVAL	FDL	VIEW		50 < L ≤ 100	±0.40