




Notes:

- 1.RoHS Compliant;
- 2.Top Hole:Ø4.75±0.08mm,
Panel Thickness:1.57mm;
- 3.Bottom Hole:Ø4.75±0.08mm,
Panel Thickness:1.57mm.

Part No.	Part Name	Part No.	Part Name	Color	A
40241	8G801V40241	41851	8G801V41851	Natural	4.8
40242	8G801V40242	41852	8G801V41852	Black	
40243	8G801V40243	41853	8G801V41853	Natural	6.4
40244	8G801V40244	41854	8G801V41854	Black	
40245	8G801V40245	41855	8G801V41855	Natural	7.9
40246	8G801V40246	41856	8G801V41856	Black	
40247	8G801V40247	41857	8G801V41857	Natural	9.5
40248	8G801V40248	41858	8G801V41858	Black	
40249	8G801V40249	41859	8G801V41859	Natural	11.1
40250	8G801V40250	41860	8G801V41860	Black	
40251	8G801V40251	41861	8G801V41861	Natural	12.7
40252	8G801V40252	41862	8G801V41862	Black	
40253	8G801V40253	41863	8G801V41863	Natural	14.3
40254	8G801V40254	41864	8G801V41864	Black	
40255	8G801V40255	41865	8G801V41865	Natural	15.9
40256	8G801V40256	41866	8G801V41866	Black	
40257	8G801V40257	41867	8G801V41867	Natural	19.1
40258	8G801V40258	41868	8G801V41868	Black	
40259	8G801V40259	41869	8G801V41869	Natural	22.2
40260	8G801V40260	41870	8G801V41870	Black	
40261	8G801V40261	41871	8G801V41871	Natural	25.4
40262	8G801V40262	41872	8G801V41872	Black	
Material: PA66 UL94 V2		Material: PA66 UL94 V0			

DREMEC Befestigungselemente GmbH						DATE	2020.03.06	DIMENSION	TOLERANCE
TITLE	DUAL LOCKING CIRCUIT BOARD SUPPORT					SCALE	FIT	L≤4	±0.10
PART NAME	8G801V40241	MOLD NO.	S0308-10	DRAW	PLK	UNIT	MM	4 < L ≤ 15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	15 < L ≤ 50	±0.30
DWG NO.	E4016	COLOR	SEE TABLE	APPROVAL	FDL	VIEW		50 < L ≤ 100	±0.40