




Notes:

- 1.Color:Natural;
- 2.RoHS Compliant;
- 3.Top Hole: $\text{Ø}3.5\pm0.05\text{mm}$,
Panel Thickness: 0.8-2.0mm;
- 4.Bottom Hole: $\text{Ø}3.5\pm0.05\text{mm}$,
Panel Thickness: 0.8-2.0mm.

Part No.	Part Name	Part No.	Part Name	A
42715	8GG01V42715	42730	8GG01V42730	4.8
42716	8GG01V42716	42731	8GG01V42731	6.4
42717	8GG01V42717	42732	8GG01V42732	7.9
42718	8GG01V42718	42733	8GG01V42733	9.5
42719	8GG01V42719	42734	8GG01V42734	11.1
42720	8GG01V42720	42735	8GG01V42735	12.7
42721	8GG01V42721	42736	8GG01V42736	14.3
42722	8GG01V42722	42737	8GG01V42737	15.9
42723	8GG01V42723	42738	8GG01V42738	22.2
Material: PA66 UL94 V2		Material: PA66 UL94 V0		

DREMEC Befestigungselemente GmbH						DATE	2020.03.16	DIMENSION	TOLERANCE
TITLE	PCB SUPPORT - LOCKING ARROWHEAD, TENSION WINGS					SCALE	FIT	$L \leq 4$	± 0.10
PART NAME	8GG01V42715	MOLD NO.	S0635	DRAW	PLK	UNIT	MM	$4 < L \leq 15$	± 0.20
PART NO.	SEE TABLE	MATERIAL	SEE NOTES	DESIGN	PLK	VERSION	A0	$15 < L \leq 50$	± 0.30
DWG NO.	E4304	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		$50 < L \leq 100$	± 0.40