




Notes:

- 1.Color:Natural;
- 2.RoHS Compliant;
- 3.Top Hole: Ø3.86±0.05mm,
Panel Thickness: 1.57mm;
- 4.Bottom Hole: Ø3.86±0.05mm,
Panel Thickness: 1.57mm.

Part No.	Part Name	Material	A
40519	8G802V40519	PA66 UL94 V2	3.2
40520	8G802V40520	PA66 UL94 V0	
40521	8G802V40521	PA66 UL94 V2	4.8
40522	8G802V40522	PA66 UL94 V0	
40523	8G802V40523	PA66 UL94 V2	6.4
40524	8G802V40524	PA66 UL94 V0	
40525	8G802V40525	PA66 UL94 V2	7.9
40526	8G802V40526	PA66 UL94 V0	
40527	8G802V40527	PA66 UL94 V2	9.5
40528	8G802V40528	PA66 UL94 V0	
40529	8G802V40529	PA66 UL94 V2	11.1
40530	8G802V40530	PA66 UL94 V0	
40531	8G802V40531	PA66 UL94 V2	12.7
40532	8G802V40532	PA66 UL94 V0	
40533	8G802V40533	PA66 UL94 V2	14.3
40534	8G802V40534	PA66 UL94 V0	
40535	8G802V40535	PA66 UL94 V2	15.9
40536	8G802V40536	PA66 UL94 V0	
40537	8G802V40537	PA66 UL94 V2	17.5
40538	8G802V40538	PA66 UL94 V0	
40539	8G802V40539	PA66 UL94 V2	19.1
40540	8G802V40540	PA66 UL94 V0	
40541	8G802V40541	PA66 UL94 V2	20.6
40542	8G802V40542	PA66 UL94 V0	
40543	8G802V40543	PA66 UL94 V2	22.2
40544	8G802V40544	PA66 UL94 V0	
40545	8G802V40545	PA66 UL94 V2	25.4
40546	8G802V40546	PA66 UL94 V0	
40547	8G802V40547	PA66 UL94 V2	28.6
40548	8G802V40548	PA66 UL94 V0	
40549	8G802V40549	PA66 UL94 V2	31.7
40550	8G802V40550	PA66 UL94 V0	
40551	8G802V40551	PA66 UL94 V2	34.9
40552	8G802V40552	PA66 UL94 V0	
40553	8G802V40553	PA66 UL94 V2	38.1
40554	8G802V40554	PA66 UL94 V0	

DREMEC Befestigungselemente GmbH						DATE	2020.03.16	DIMENSION	TOLERANCE
TITLE	MINI SUPPORT POST					SCALE	FIT	L≤4	±0.10
PART NAME	8G802V40519	MOLD NO.	S0318-20	DRAW	PLK	UNIT	MM	4 < L ≤ 15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	15 < L ≤ 50	±0.30
DWG NO.	E4031	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		50 < L ≤ 100	±0.40