





- Notes:
1. Color:Natural;
 2. RoHS Compliant;
 3. Top Hole: Ø3.9±0.05mm,
Panel Thickness: 1.57mm;
 4. Bottom Hole: Ø3.9±0.05mm,
Panel Thickness: 1.57mm.

PartNo.	Part Name	PartNo.	Part Name	A
43260	8GG01V43260	43440	8GG01V43440	3.2
43261	8GG01V43261	43441	8GG01V43441	4.8
43262	8GG01V43262	43442	8GG01V43442	6.4
43263	8GG01V43263	43443	8GG01V43443	7.9
43264	8GG01V43264	43444	8GG01V43444	9.5
43265	8GG01V43265	43445	8GG01V43445	11.1
43266	8GG01V43266	43446	8GG01V43446	12.7
43267	8GG01V43267	43447	8GG01V43447	15.9
43268	8GG01V43268	43448	8GG01V43448	17.5
43269	8GG01V43269	43449	8GG01V43449	19.1
43270	8GG01V43270	43450	8GG01V43450	22.2
43271	8GG01V43271	43451	8GG01V43451	25.4
43209	8GG01V43209	43452	8GG01V43452	31.8
43272	8GG01V43272	43453	8GG01V43453	34.9
Material: PA66 UL94V2		Material: PA66 UL94V0		

DREMEC Befestigungselemente GmbH						DATE	2020.03.16	DIMENSION	TOLERANCE
TITLE	MINIATURE SUPPORT POST					SCALE	FIT	L≤4	±0.10
PART NAME	8GG01V43260	MOLD NO.	S1025	DRAW	PLK	UNIT	MM	4 < L ≤ 15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	15 < L ≤ 50	±0.30
DWG NO.	E4330	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		50 < L ≤ 100	±0.40