





Notes:

- 1.Material:PA66 UL94 V2;
- 2.Color:Natural;
- 3.RoHS Compliant;
- 4.Top Hole: Ø4.0±0.08mm,
Panel Thickness: 1.57mm;
- 5.Bottom Hole: See Mounting Key Slot Detail,
Panel Thickness: 1.57mm.

RECOMMENDED
MTG. SLOT

Part No.	Part Name	A
40978	8GG02V40978	3.2
40979	8GG02V40979	6.4
40980	8GG02V40980	9.5
40981	8GG02V40981	12.7

DREMEC Befestigungselemente GmbH

DATE

2020.03.16

DIMENSION

TOLERANCE

TITLE KEY SLOT LOCKING SUPPORT POST

SCALE

FIT

L≤4

±0.10

PART NAME 8GG02V40978

MOLD NO.

S0646

DRAW

PLK

UNIT

MM

4<L≤15

±0.20

PART NO. SEE TABLE

MATERIAL

SEE NOTES

DESIGN

PLK

VERSION

A0

15<L≤50

±0.30

DWG NO. E4186


COLOR

SEE NOTES

APPROVAL

FDL

VIEW



50<L≤100

±0.40