



Notes:

- 1.Material:PA66 UL94 V2;
- 2.Color:Natural;
- 3.RoHS Compliant;
- 4.Top Hole:Ø4.0±0.08mm,
Panel Thickness:1.57mm;
- 5.Bottom Hole: See Mounting Key Slot Detail,
Panel Thickness:1.57mm.



RECOMMENDED
MOUNTING SLOT

PartNo.	Part Name	A
42746	8GG01V42746	4.8
42747	8GG01V42747	6.4
42748	8GG01V42748	9.5
42749	8GG01V42749	12.7
42750	8GG01V42750	15.9

DREMEC Befestigungselemente GmbH

DATE

2020.03.16

DIMENSION

TOLERANCE

TITLE

KEY SLOT LOCKING SUPPORT POST

SCALE

FIT

L≤4

±0.10

PART NAME

8GG01V42746

MOLD NO.

S0633

DRAW

PLK

UNIT

MM

4<L≤15

±0.20

PART NO.

SEE TABLE

MATERIAL

SEE NOTES

DESIGN

PLK

VERSION

A0

15<L≤50

±0.30

DWG NO.

E4306


COLOR

SEE NOTES

APPROVAL

FDL

VIEW



50<L≤100

±0.40