


Notes:
1.Color:Natural;
2.RoHS Compliant;
3.Top Hole: Ø4.0±0.08mm,
Panel Thickness: 1.57mm;
4.Bottom Hole: Ø7.92±0.08mm,
Panel Thickness: 6.4mm min.

Part No.	Part Name	Part No.	Part Name	A
41113	8G812V41113	41606	8G812V41606	4.8
41114	8G812V41114	41607	8G812V41607	6.4
41115	8G812V41115	41608	8G812V41608	9.5
41116	8G812V41116	41609	8G812V41609	11.1
41117	8G812V41117	41610	8G812V41610	12.7
41118	8G812V41118	41611	8G812V41611	15.9
41119	8G812V41119	41612	8G812V41612	19.1
41120	8G812V41120	41613	8G812V41613	22.2
Material: PA66 UL94 V2		Material: PA66 UL94 V0		

DREMEC Befestigungselemente GmbH						DATE	2020.03.16	DIMENSION	TOLERANCE
TITLE	BLIND HOLE CIRCUIT BOARD SUPPORT					SCALE	FIT	L≤4	±0.10
PART NAME	8G812V41113	MOLD NO.	S0478	DRAW	JF	UNIT	MM	4<L≤15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	JF	VERSION	A0	15<L≤50	±0.30
DWG NO.	E4115	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		50<L≤100	±0.40