


Notes:

- 1.Color:Natural;
- 2.RoHS Compliant;
- 3.Top Hole: $\text{Ø}4.0\pm0.08\text{mm}$,
Panel Thickness: 0.79-1.98mm;
- 4.Bottom Hole: $\text{Ø}7.92\pm0.08\text{mm}$,
Panel Thickness: 6.4mm min.

Part No.	Part Name	Part No.	Part Name	A
41121	8G812V41121	41614	8G812V41614	6.4
41122	8G812V41122	41615	8G812V41615	9.5
41123	8G812V41123	41616	8G812V41616	12.7
41124	8G812V41124	41617	8G812V41617	15.9
41125	8G812V41125	41618	8G812V41618	19.1
41126	8G812V41126	41619	8G812V41619	22.2
Material: PA66 UL94 V2		Material: PA66 UL94 V0		

DREMEC Befestigungselemente GmbH						DATE	2020.03.16	DIMENSION	TOLERANCE
TITLE	BLIND HOLE CIRCUIT BOARD SUPPORT					SCALE	FIT	$L \leq 4$	± 0.10
PART NAME	8G812V41121	MOLD NO.	S0505	DRAW	JF	UNIT	MM	$4 < L \leq 15$	± 0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	JF	VERSION	A0	$15 < L \leq 50$	± 0.30
DWG NO.	E4116	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		$50 < L \leq 100$	± 0.40