






TAPE 17.0*17.0A*1.0MM

Notes:

- 1.Material: RUBBER +TAPE;
- 2.Color: Natural;
- 3.RoHS Compliant;
- 4.Top Hole: $\text{Ø}4.0\pm0.08\text{mm}$,
Panel Thickness: 1.57mm.

Part No.	Article No.	A
43353	8GB07V43353	4.8
43354	8GB07V43354	6.0
43355	8GB07V43355	6.4
43356	8GB07V43356	8.0
43357	8GB07V43357	9.5
43358	8GB07V43358	10.0
43359	8GB07V43359	12.0
43360	8GB07V43360	12.7
43361	8GB07V43361	14.0
43362	8GB07V43362	15.9
43418	8GB07V43418	16.0
43363	8GB07V43363	19.1
43364	8GB07V43364	22.2
43365	8GB07V43365	25.4
43366	8GB07V43366	28.6

DREMEC Befestigungselemente GmbH						DATE	2020.03.16	DIMENSION	TOLERANCE
TITLE	PUSH SPACER ON ADHESIVE BASE					SCALE	FIT	$L \leq 4$	± 0.10
ARTICLE NO.	8GB07V43353	MOLD NO.	S0472	DRAW	JF	UNIT	MM	$4 < L \leq 15$	± 0.20
PART NO.	SEE TABLE	MATERIAL	SEE NOTES	DESIGN	JF	VERSION	A0	$15 < L \leq 50$	± 0.30
DWG NO.	E4091	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		$50 < L \leq 100$	± 0.40