






Part No.	Part Name	Part No.	Part Name	Material	A
40303	8G504V40303	41913	8G504V41913	PA66 UL94 V2	6.4
40304	8G504V40304	41914	8G504V41914	PA66 UL94 V0	
40305	8G504V40305	41915	8G504V41915	PA66 UL94 V2	
40306	8G504V40306	41916	8G504V41916	PA66 UL94 V0	9.5
40307	8G504V40307	41917	8G504V41917	PA66 UL94 V2	
40308	8G504V40308	41918	8G504V41918	PA66 UL94 V0	12.7
40309	8G504V40309	41919	8G504V41919	PA66 UL94 V2	
40310	8G504V40310	41920	8G504V41920	PA66 UL94 V0	15.9
40311	8G504V40311	41921	8G504V41921	PA66 UL94 V2	
40312	8G504V40312	41922	8G504V41922	PA66 UL94 V0	19.1
42101	8G504V42101	41523	8G504V41523	PA66 UL94 V2	
42102	8G504V42102	42725	8G504V42725	PA66 UL94 V0	20.4
40313	8G504V40313	41923	8G504V41923	PA66 UL94 V2	
40314	8G504V40314	41924	8G504V41924	PA66 UL94 V0	22.2
40315	8G504V40315	41925	8G504V41925	PA66 UL94 V2	
40316	8G504V40316	41926	8G504V41926	PA66 UL94 V0	25.4
40317	8G504V40317	41927	8G504V41927	PA66 UL94 V2	
40318	8G504V40318	41928	8G504V41928	PA66 UL94 V0	28.6
40319	8G504V40319	41929	8G504V41929	PA66 UL94 V2	
40320	8G504V40320	41930	8G504V41930	PA66 UL94 V0	35.7 ⁺⁰ _{-0.6}
Color: Natural		Color: Black			

Notes:

- 1.RoHS Compliant;
- 2.Top Hole: Ø4.0±0.08mm,
Panel Thickness:1.57mm.

DREMEC Befestigungselemente GmbH						DATE	2020.03.22	DIMENSION	TOLERANCE
TITLE	LOCKING CIRCUIT BOARD SUPPORT THREADED MALE					SCALE	FIT	L ≤4	±0.10
PART NAME	8G504V40303	MOLD NO.	S0313/350	DRAW	PLK	UNIT	MM	4 < L ≤15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	15 < L ≤50	±0.30
DWG NO.	E4019	COLOR	SEE TABLE	APPROVAL	FDL	VIEW		50 < L ≤100	±0.40