



Notes:

- 1.RoHS Compliant;
- 2.Hole: $\text{Ø}4.0\pm0.08\text{mm}$,
Panel Thickness: 1.57mm.

Part No.	Part Name	Part No.	Part Name	Material	A
40321	8G504V40321	41931	8G504V41931	PA66 UL94 V2	6.4
40322	8G504V40322	41932	8G504V41932	PA66 UL94 V0	
40323	8G504V40323	41933	8G504V41933	PA66 UL94 V2	9.5
40324	8G504V40324	41934	8G504V41934	PA66 UL94 V0	
40325	8G504V40325	41935	8G504V41935	PA66 UL94 V2	12.7
40326	8G504V40326	41936	8G504V41936	PA66 UL94 V0	
40327	8G504V40327	41937	8G504V41937	PA66 UL94 V2	15.9
40328	8G504V40328	41938	8G504V41938	PA66 UL94 V0	
40329	8G504V40329	41939	8G504V41939	PA66 UL94 V2	19.1
40330	8G504V40330	41940	8G504V41940	PA66 UL94 V0	
42550	8G504V42550	42726	8G504V42726	PA66 UL94 V2	20.4
42551	8G504V42551	42727	8G504V42727	PA66 UL94 V0	
40331	8G504V40331	41941	8G504V41941	PA66 UL94 V2	22.2
40332	8G504V40332	41942	8G504V41942	PA66 UL94 V0	
40333	8G504V40333	41943	8G504V41943	PA66 UL94 V2	25.4
40334	8G504V40334	41944	8G504V41944	PA66 UL94 V0	
40335	8G504V40335	41945	8G504V41945	PA66 UL94 V2	28.6
40336	8G504V40336	41946	8G504V41946	PA66 UL94 V0	
40337	8G504V40337	42728	8G504V42728	PA66 UL94 V2	35.7 ⁺⁰ _{-0.6}
40338	8G504V40338	42729	8G504V42729	PA66 UL94 V0	
Color: Natural		Color: Black			

DREMEC Befestigungselemente GmbH						DATE	2020.03.22	DIMENSION	TOLERANCE
TITLE	LOCKING CIRCUIT BOARD SUPPORT THREADED MALE					SCALE	FIT	$L \leq 4$	± 0.10
PART NAME	8G504V40321	MOLD NO.	S0313/350	DRAW	PLK	UNIT	MM	$4 < L \leq 15$	± 0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	$15 < L \leq 50$	± 0.30
DWG NO.	E4020	COLOR	SEE TABLE	APPROVAL	FDL	VIEW		$50 < L \leq 100$	± 0.40