





Notes:
1.RoHS Compliant;
2.Hole:Ø3.18±0.05mm;
Panel Thickness:1.57mm;



Part No.	Part Name	Part No.	Part Name	Part No.	Part Name	Part No.	Part Name	A
41165	8G505V41165	41690	8G505V41690	41708	8G505V41708	41726	8G505V41726	3.2
41166	8G505V41166	41691	8G505V41691	41709	8G505V41709	41727	8G505V41727	4.8
41167	8G505V41167	41692	8G505V41692	41710	8G505V41710	41728	8G505V41728	6.4
41168	8G505V41168	41693	8G505V41693	41711	8G505V41711	41729	8G505V41729	7.9
41169	8G505V41169	41694	8G505V41694	41712	8G505V41712	41730	8G505V41730	9.5
41170	8G505V41170	41695	8G505V41695	41713	8G505V41713	41731	8G505V41731	11.1
41171	8G505V41171	41696	8G505V41696	41714	8G505V41714	41732	8G505V41732	12.7
41172	8G505V41172	41697	8G505V41697	41715	8G505V41715	41733	8G505V41733	14.3
41173	8G505V41173	41698	8G505V41698	41716	8G505V41716	41734	8G505V41734	15.9
Material:PA66 UL94V2 Color:Natural		Material:PA66 UL94V0 Color:Natural		Material:PA66 UL94V2 Color:Black		Material:PA66 UL94V0 Color:Black		

DREMEC Befestigungselemente GmbH						DATE	2020.03.22	DIMENSION	TOLERANCE
TITLE	LOCKING CIRCUIT BOARD SUPPORT THREADED MALE					SCALE	FIT	L≤4	±0.10
PART NAME	8G505V41165	MOLD NO.	S0517	DRAW	ZHR	UNIT	MM	4<L≤15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	ZHR	VERSION	A0	15<L≤50	±0.30
DWG NO.	E4122	COLOR	SEE TABLE	APPROVAL	FDL	VIEW		50<L≤100	±0.40