





Notes:
1.RoHS Compliant;
2.Hole:Ø3.18±0.05mm;
Panel Thickness:1.57mm;



Part No.	Part Name	Part No.	Part Name	Part No.	Part Name	Part No.	Part Name	A
41174	8G505V41174	41699	8G505V41699	41717	8G505V41717	41735	8G505V41735	3.2
41175	8G505V41175	41700	8G505V41700	41718	8G505V41718	41736	8G505V41736	4.8
41176	8G505V41176	41701	8G505V41701	41719	8G505V41719	41737	8G505V41737	6.4
41177	8G505V41177	41702	8G505V41702	41720	8G505V41720	41738	8G505V41738	7.9
41178	8G505V41178	41703	8G505V41703	41721	8G505V41721	41739	8G505V41739	9.5
41179	8G505V41179	41704	8G505V41704	41722	8G505V41722	41740	8G505V41740	11.1
41180	8G505V41180	41705	8G505V41705	41723	8G505V41723	41741	8G505V41741	12.7
41181	8G505V41181	41706	8G505V41706	41724	8G505V41724	41742	8G505V41742	14.3
41182	8G505V41182	41707	8G505V41707	41725	8G505V41725	41743	8G505V41743	15.9
Material:PA66 UL94V2 Color:Natural		Material:PA66 UL94V0 Color:Natural		Material:PA66 UL94V2 Color:Black		Material:PA66 UL94V0 Color:Black		

DREMEC Befestigungselemente GmbH

DATE

2020.03.22

DIMENSION

TOLERANCE

TITLE LOCKING CIRCUIT BOARD SUPPORT THREADED MALE

SCALE

FIT

$L \leq 4$

± 0.10

PART NAME 8G505V41174 MOLD NO. S0517 DRAW ZHR

UNIT

MM

$4 < L \leq 15$

± 0.20

PART NO. SEE TABLE MATERIAL SEE TABLE DESIGN ZHR

VERSION


A0

$15 < L \leq 50$

± 0.30

DWG NO. E4123 COLOR SEE TABLE APPROVAL FDL

VIEW



$50 < L \leq 100$

± 0.40