





Part No.	Part Name	Part No.	Part Name	A
42415	8G519V42415	42421	8G519V42421	9.5
42416	8G519V42416	42422	8G519V42422	12.7
42417	8G519V42417	42423	8G519V42423	15.9
42418	8G519V42418	42424	8G519V42424	19.1
42419	8G519V42419	42425	8G519V42425	22.2
42420	8G519V42420	42426	8G519V42426	25.4
M Thread: #6-32		M Thread: M4		

Notes:
 1.Material:PA66 UL94 V2;
 2.Color:Natural;
 3.RoHS Compliant;
 4.Hole:Ø4.0±0.08mm,
 Panel Thickness:1.57mm;



This position doesn't
exist once A=9.5mm

DREMEC Befestigungselemente GmbH						DATE	2020.03.22	DIMENSION	TOLERANCE
TITLE	LOCKING CIRCUIT BOARD SUPPORT THREADED FEMALE					SCALE	FIT	L ≤ 4	±0.10
PART NAME	8G519V42415	MOLD NO.	S0611	DRAW	ZHR	UNIT	MM	4 < L ≤ 15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE NOTES	DESIGN	ZHR	VERSION	A0	15 < L ≤ 50	±0.30
DWG NO.	E4160	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		50 < L ≤ 100	±0.40