




Notes:

- 1.RoHS Compliant;
- 2.Top Hole:Ø2.5±0.05mm;
Panel Thickness:1.6mm;

Part No.	Part Name	Part No.	Part Name	Part No.	Part Name	Part No.	Part Name	A
41233	8G506V41233	41797	8G506V41797	41806	8G506V41806	41815	8G506V41815	3.2
41234	8G506V41234	41798	8G506V41798	41807	8G506V41807	41816	8G506V41816	4.8
41235	8G506V41235	41799	8G506V41799	41808	8G506V41808	41817	8G506V41817	6.4
41236	8G506V41236	41800	8G506V41800	41809	8G506V41809	41818	8G506V41818	7.9
41237	8G506V41237	41801	8G506V41801	41810	8G506V41810	41819	8G506V41819	9.5
41238	8G506V41238	41802	8G506V41802	41811	8G506V41811	41820	8G506V41820	11.1
41239	8G506V41239	41803	8G506V41803	41812	8G506V41812	41821	8G506V41821	12.7
41240	8G506V41240	41804	8G506V41804	41813	8G506V41813	41822	8G506V41822	14.3
41241	8G506V41241	41805	8G506V41805	41814	8G506V41814	41823	8G506V41823	15.9
Material: PA66 UL94 V2 Color: Natural		Material: PA66 UL94 V0 Color: Natural		Material: PA66 UL94 V2 Color: Black		Material: PA66 UL94 V0 Color: Black		

DREMEC Befestigungselemente GmbH

DATE

2020.03.26

DIMENSION

TOLERANCE

TITLE

MINI THREADED CIRCUIT BOARD SUPPORT

SCALE

FIT

$L \leq 4$

±0.10

PART NAME

8G506V41233

MOLD NO.

S0508

DRAW

ZHR

UNIT

MM

$4 < L \leq 15$

±0.20

PART NO.

SEE TABLE

MATERIAL

SEE TABLE

DESIGN

ZHR

VERSION

A0

$15 < L \leq 50$

±0.30

DWG NO.

E4137


COLOR

SEE TABLE

APPROVAL

FDL

VIEW



$50 < L \leq 100$

±0.40