


Notes:

- 1.Color:Natural;
- 2.RoHS Compliant;
- 3.Top Hole: $\text{Ø}4.0\pm0.08\text{mm}$,
Panel Thickness: 0.79-1.98mm;
- 4.Bottom Hole: $\text{Ø}6.35\pm0.08\text{mm}$,
Panel Thickness: 6.4mm min.

Part No.	Part Name	Part No.	Part Name	A
41143	8G812V41143	41636	8G812V41636	6.4
41144	8G812V41144	41637	8G812V41637	9.5
41145	8G812V41145	41638	8G812V41638	12.7
41146	8G812V41146	41639	8G812V41639	15.9
41147	8G812V41147	41640	8G812V41640	19.1
41148	8G812V41148	41641	8G812V41641	22.2
Material: PA66 UL94 V2		Material: PA66 UL94 V0		

DREMEC Befestigungselemente GmbH						DATE	2020.03.16	DIMENSION	TOLERANCE
TITLE	BLIND HOLE CIRCUIT BOARD SUPPORT					SCALE	FIT	$L \leq 4$	± 0.10
PART NAME	8G812V41143	MOLD NO.	S0505	DRAW	JF	UNIT	MM	$4 < L \leq 15$	± 0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	JF	VERSION	A0	$15 < L \leq 50$	± 0.30
DWG NO.	E4119	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		$50 < L \leq 100$	± 0.40