

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2135230001](#)
Status: **Active**
Overview: [LTE Cellular Antennas](#)
Description: 698MHz-2.7GHz LTE Hinged External Antenna, with SMA Male Connector, Black

Documents:
[3D Model](#) [Application Specification 2135230001-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [Packaging Specification 2135230001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification 2135230001-001 \(PDF\)](#)

General
Product Family Antennas
Series [213523](#)
Component Type External Antenna
Function Signal
Mates With SMA Female Receptacle
Overview [LTE Cellular Antennas](#)
Product Name LTE Cellular Antenna
Protocol Cellular
Type External Antenna
UPC 193264345298

Physical
Length 171.50mm
Mounting Style N/A
Net Weight 14.143/g
Packaging Type PET Bag
Polarization Linear
Radiation Pattern Omnidirectional
Width 19.40mm

Electrical
Band#1 F_End (MHz) 960
Band#1 F_Start (MHz) 698
Band#2 F_End (MHz) 2690
Band#2 F_Start (MHz) 1710
Electrical Connectivity Cable
Peak Gain (dBi) 2.3 @ 698 MHz, 4.8 @ 1710 MHz
Return Loss - S11 (dB) < -10, < -5
Total Efficiency >55% @ 698 MHz, >70% @ 1710 MHz

Material Info

Reference - Drawing Numbers
Application Specification 2135230001-000
Packaging Specification 2135230001-001
Product Specification 2135230001-001
Sales Drawing 2135230001-000



EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)4578-DC (25 June 2020)	
Lead	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[213523](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION