




DIN 963 A

~ISO 2009

8.8

Standard withdrawn



BN 363

Slotted flat countersunk head machine screws

Steel 8.8

zinc plated blue

- ~UNI 6109
- ~ČSN 021151

 [3D Cadenas](#)


All lengths fully threaded
Countersink must be designed according to the corresponding standard!

Article#	d ₁	d ₂ max.	k max.	n	t min.	L
1143565	M2,5	4,7	1,5	0,6	0,5	4
1143573						5
1143581						6
1143603						8
1143611						10
1143638						12
1143654						16
1143840	M3	5,6	1,65	0,8	0,6	5
1143859						6
1143867						8
1143875						10
1143883						12
1143905						16
1143921						20
1143956						25
1144111	M4	7,5	2,2	1	0,8	6
1144138						8
1144146						10
1144154						12
1144170						16
1144197						20
1144227						30
1144235						35

Article#	d ₁	d ₂ max.	k max.	n	t min.	L
1144286	M5	9,2	2,5	1,2	1	8
1144294						10
1144308						12
1144324						16
1144340						20
1144367						25
1144375						30
1144383						35
1144391						40
1144448	M6	11	3	1,6	1,2	10
1144456						12
1144472						16
1144499						20
1144510						25
1144529						30
1144537						35
1144545						40