

1

2


3

4



5

6


7

FOR
客户名称APPROVED
客户确认签字ATTN
销售负责人

The shaded part is illuminated



PANEL CUTOUT



Seal Ring

"□"	Electrical Function
10B	NO Momentary(Low Level)
Other function can be made to order	

Part Number:ONPOW91-30D□YSS△▲

"△"			
1 LED		2 LED	
NR	Non-illum./Red	RG	Red/Green
NG	Non-illum./Green	GR	Green/Red
Other LED can be made to order			


"▲"	Lamp Voltage
6V	DC 6V
12V	DC 12V
24V	DC 24V

SPECIFICATIONS:

- 1.Switch Rating: DC6~24V/300mA.
- 2.Life: ≥1,000,000cycles.
- 3.Reaction Distance: 2~15cm.
- 4.Operation mode: NO Momentary.
- 5.Insulation Resistance: ≥1,000MΩ.
- 6.Dielectric Strength: 1,500V, RMS 50Hz, 1min.
- 7.Operating Temperature: -15°C~ +55°C(No Freezing).
- 8.Torque: About 0.6Nm max.applied to nut.
- 9.Protection degree: IP65.
- 10.Terminal Type: Sheltered cable.

MATERIALS:

- 1.Head: PMMA.
- 2.Body: Stainless Steel.

Wiring instructionsBRAND
品牌 **ONPOW****红波按钮制造有限公司**
ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF ONPOW PUSH
BUTTON MANUFACTURE CO.,LTD. AND
SHALL NOT BE REPRODUCED COPIED OR
USED IN ANY MANNER WITHOUT THE
PRIOR WRITTEN CONSENT OF ONPOW
PUSH BUTTON MANUFACTURE CO.,LTD.

USED
用途
FINISH
处理
SCALE
比例 1.2 : 1
UNIT
单位 mm
APPD
审核 CH 2020/06/17
CHKD
校对 NCH 2020/06/17
DR.
制图 ZPD 2020/06/17

DIMENSIONS	TOLERANCE
0.00 TO 18.00mm	±0.43mm
18.01 TO 30.00mm	±0.52mm
30.01 TO 50.00mm	±0.62mm
50.01 TO 80.00mm	±0.74mm

TITLE 名称	Contactless sensor switch	
DWG NO. 图号	ONPOW91-30D低电平	
FILE NAME 档案名称	ONPOW91-30D.DWG	SHEET 张 1 / 1
REV. 更改	1	SIZE 图纸 A4