




DIN 32501-1

~ISO 13918 PT

37-3

Norm zurückgezogen



BN 1456


Schweissbolzen

Spitzenzündung, mit Aussengewinde

Stahl 37-3

verkupfert

3D Cadenas



1. Vor dem Schweissen
2. Nach dem Schweissen
3. Masse
4. Spannzange
5. Befestigungselement
6. Zündspitze
7. Werkstück

Article#	Customer Article#	d ₁	d ₂	h	L
1107763		M3	4,5	0,7-1,4	6
1107771					8
1107798					10
1107801					12
1107828					(15)
1674412					16
1107836					20
1107844					25
1107852		M4	5,5	0,7-1,4	8
1107860					10
1107879					12
1107887					(15)

Article#	Customer Article#	d ₁	d ₂	h	L
1674420		M4	5,5	0,7-1,4	16
1107895					20
1107909					25
1107917					30
1107941		M5	6,5	0,8-1,4	8
1107968					10
1107976					12
1107984					(15)
1674439					16
1107992					20
1108018					25
1108026					30
1108050		M6	7,5	0,8-1,4	10
1108069					12
1108077					(15)
1674528					16
1108085					20
1108093					25
1108107					30
1108123					40
1108158					50
1108166		M8	9	~1	10
1108174					(15)
1674846					16
1108182					20
1108190					25
1108204					30
1108603					35
1108611					40