



EAN:	4013288032980	Size:	45x8x8 mm
Part number:	05064175001	Weight:	12 g
Article number:	867/15 TORX®	Country of origin:	CZ
		Customs tariff number:	82079030

- For recessed TORX® screws
- Ductile and tough for hard materials
- Thread drive M 6 (Wera connecting series 15)
- Suitable for Böllhoff/Uniquick, Holz-Her, Weber
- Prevents premature breakage of the drive tip

High quality bits for recessed TORX® screws. Tough viscous for universal use. Thread drive M 6.

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_torx_screws_867_15_torx.html

Wera - 867/15 TORX®
05064175001 - 4013288032980

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 /

Bits for TORX® Screws

Thread drive M 6 (Wera connecting series 15)



Thread drive M 6 (Wera connecting series 15). Drive: For direct machine drive. Suitable for: Böllhoff/Uniquick, Holz-Her, Weber.

Tough-absorbing bits



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

Further versions in this product family:

				
		mm	inch	mm
05064166001	TX 10	45	1 3/4	8.0
05064168001	TX 15	45	1 3/4	8.0
0506417				