



391-T42_M

Abrasive High-Performance Cutting Discs for Metal



PRODUCT DETAILS

- High performance discs for cutting all types of metal
- High performance discs for cutting all types of metal
- Extended product life resulting in less downtime and waste
- Reduced risk of muscle fatigue due to low vibration
- Free of Iron, Sulphur and Chloride
- OSA certified, in accordance with EN12413



PRODUCT ATTRIBUTES

Product				
3911-115-T42-M	115 mm	2,5 mm	22,23 mm	62 g
3911-180-T42-M	180 mm	3,2 mm	22,23 mm	190 g
3911-125-T42-M	125 mm	2,5 mm	22,23 mm	73 g
3911-230-T42-M	230 mm	3,2 mm	22,23 mm	320 g
3911-150-T42-M	150 mm	2,5 mm	22,23 mm	106 g

Follow the Fish!

