



392-T27_IM

Abrasive High-Performance Grinding Discs for Inox & Metal



PRODUCT DETAILS

- High performance discs for grinding in all types of stainless steel and metal
- Optimal material removal rate
- Extended product life resulting in less downtime and waste.
- Reinforced glass fiber fabrics for maximum safety high and stability
- Reduced risk of muscle fatigue due to low vibration
- Free of Iron, Sulphur and Chloride
- OSA certified, in accordance with EN12413



PRODUCT ATTRIBUTES

Product				
3921-115-T27-IM	115 mm	6,4 mm	22,23 mm	148 g
3921-180-T27-IM	180 mm	6,5 mm	22,23 mm	370 g
3921-125-T27-IM	125 mm	6,4 mm	22,23 mm	175 g
3921-230-T27-IM	230 mm	6,5 mm	22,23 mm	610 g
3921-150-T27-IM	150 mm	6,4 mm	22,23 mm	256 g

Follow the Fish!

