

# MG 130

Product no.: 130-1000-ESDN



## Benefits

- › 100–240 power supply for global use
- › Filter alarm and 3 steps speed control
- › Small foot print design
- › The fume extraction unit MG 130 is easy to install and operate. Is supplied complete ready to place close to the workbench.



## Technical Data

|                                  |                                                                                 |
|----------------------------------|---------------------------------------------------------------------------------|
| Dimensions L x W x H (mm)        | 460 x 210 x 500                                                                 |
| Dimensions L x W x H (inches)    | 18,11 x 8,26 x 19,68                                                            |
| Weight (approx.) in kg           | 11                                                                              |
| Voltage                          | 100 - 240 V, 50/60 Hz                                                           |
| Power                            | 100 W                                                                           |
| Noise level (distance 1 m) dB(A) | < 52                                                                            |
| Max. vacuum                      | ---                                                                             |
| Capacity m³/h                    | 140                                                                             |
| Pre-filter                       | Pre filter mat class F7                                                         |
| Compact filter                   | Particle filter H13, Wide band gas filter (50 % Active carbon + 50 % Chemisorb) |
| Max. capacity                    | 1-2 workstations                                                                |
| RS232 interface (remote control) | 1 x RS232 (TTL)                                                                 |
| USB port                         | ---                                                                             |
| WX-compatible                    | ---                                                                             |
|                                  |                                                                                 |