

Technical Datasheet **RoHS₃** **tasker® TSK1147 – 4x0,08 mm² Miniature Cable**



CATEGORY Miniature Cable (See Audio Catalogue)
APPLICATIONS Earphones, headphones and electronics.

- A:** Outer PET soft Jacket Braid – Color Black.
B: Soft **PVC** compound material Black color.
 Outer cable Diam. Ø 2,00 (±0,10) mm.
C: Each conductor is enameled with different color: Red, Green, Blue, Yellow.
 Diam. Ø: 0,40 (±0,10) mm. Red copper + Kevlar formation 16x0,08 mm.
 Nom. Cross section 4x0,08 mm².

MARKING **tasker®** TSK1147 – 4x0,08 mm² - O.F.C. + Kevlar – Micro Audio Cable
CUSTOM This product may be custom produced also in **LSZH, PE, PUR**,
PRODUCTION with or without Metallic Armor.

Cable Properties

Conductor Resistance	203 Ω/Km
Pair Capacity	87 pF/m
Tensile Load with PET Braid	18,00 Kg
Tensile Load of Row Cable	7,00 Kg
Max Rated Voltage	30 V
Operative Temperature	-20/+80°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. D / 02.12.20
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			