

MILAN S.r.l. a socio unico

Head Office – Export department:

Viale Europa, 74
20090 Cusago (MI) Italy
T. +39 02 9039.4556-4158
F. +39 02 9039.4551
www.taskercables.com

Ufficio Commerciale e Centro Distribuzione

Viale Europa 72 Strada F12
20090 Cusago (MI) Italy
T. +39 02 9039.0037-0059
F. +39 02 9039.0049
www.tasker.it

Technical Datasheet

tasker® C131 – 1x0,35 mm²

Flexible Unipolar Cable

✓
RoHS₂
2002/95/EC
2011/65/UE



CATEGORY Unipolar Cable (See Electronic Catalogue)
APPLICATIONS Electronics and Wiring.

A: Soft **PVC HT105°C** Sheath. – Available in different color.
Outer cable Diam. Ø 1,40 (±0,10) mm.

B: O.F.C. Red Copper stranded formation with 0,20 mm elementary wires.
Nom. Cross section 1x0,35 mm².

MARKING not marked
CUSTOM This product may be custom produced also in **L.S.Z.H.** polymer, **PE**, **PUR**,
PRODUCTION or Metallic Armored.

Cable Properties

Conductor Resistance	58,00 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-20/+105°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. A / 26.05.17
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			