



MILAN S.r.l. a socio unico

Head Office – Export department:

Viale Europa, 74  
20090 Cusago (MI) Italy  
T. +39 02 9039.4556-4158  
F. +39 02 9039.4551  
www.taskercables.com

Ufficio Commerciale e Centro Distribuzione

Viale Europa 72 Strada F12  
20090 Cusago (MI) Italy  
T. +39 02 9039.0037-0059  
F. +39 02 9039.0049  
www.tasker.it

✓  
RoHS<sub>2</sub>  
2002/95/EC  
2011/65/UE



**Firestop®**

**Technical Datasheet**

**tasker® C1025 CPR – 1x0,25 mm<sup>2</sup>**  
**Braided Shielded Cable**



| A | B | C | D |
|---|---|---|---|
|---|---|---|---|

**CATEGORY**  
**APPLICATIONS**

Braided Conductor Shielded Cable (See Data Network Catalogue)

Data transmission and Electronics

- A:** Black **Flame Retardant PVC** sheath.  
Outer cable diam. Ø 3,00 (±0,20) mm.
- B:** Braided Shielding O.F.C. Red Copper covering 85%.
- C:** Cores Insulation with **Flame Retardant PVC**.  
Core color code with DIN 47100 Standards.  
Diam. Ø 1,40 (±0,20) mm.
- D:** Stranded O.F.C. Red Copper formation 8x0,20 mm.  
Nom. Cross section 1x0,25 mm<sup>2</sup>.

**MARKING**

**tasker® C1025 CPR 1x0,25 mm<sup>2</sup> O.F.C. - IMQ 0051-CPR-0961 – 2017 – Eca –**  
**BRAIDED SHIELDED CABLE - Firestop® - Made Italy**

**Cable Properties**

|                              |           |
|------------------------------|-----------|
| <b>Conductor Resistance</b>  | 75 Ω/Km   |
| <b>Capacity Core/Shield</b>  | 240 pF/mt |
| <b>Max Rated Voltage</b>     | 49 V      |
| <b>Operative Temperature</b> | -20/+70°C |

|                |          |                       |                   |
|----------------|----------|-----------------------|-------------------|
| <b>USE</b>     | <b>X</b> | Indoor                | Interno Edificio  |
| <b>Impiego</b> | <b>X</b> | Outdoor Limited       | Esterno Limitato  |
|                |          | Outdoor               | Esterno           |
|                |          | Outdoor Direct Burial | Esterno Interrato |

|                     |          |                      |                  |
|---------------------|----------|----------------------|------------------|
| <b>INSTALLATION</b> | <b>X</b> | Fixed                | Fissa            |
| <b>Posa</b>         | <b>X</b> | Restricted Mobile    | Mobile Limitata  |
|                     |          | Mobile               | Mobile           |
|                     |          | Mobile in Drag Chain | Mobile in Catena |

|                     |          |                   |
|---------------------|----------|-------------------|
| <b>INFORMATION</b>  | <b>X</b> | RoHS2 Compliant   |
| <b>Informazioni</b> | <b>X</b> | Ver. A / 12.10.17 |
|                     |          |                   |
|                     |          |                   |