

MILAN S.r.l. a socio unico

Head Office – Export department:

Viale Europa, 74
20090 Cusago (MI) Italy
T. +39 02 9039.4556-4158
F. +39 02 9039.4551
www.taskercables.com

Ufficio Commerciale e Centro Distribuzione

Viale Europa 72 Strada F12
20090 Cusago (MI) Italy
T. +39 02 9039.0037-0059
F. +39 02 9039.0049
www.tasker.it

Technical Datasheet



tasker® C117 - 2x0,10 mm² - Shielded Flat Audio Cable



A	B	C	D
---	---	---	---

CATEGORY

Shielded Flat Audio Cables (See Audio Catalogue)

APPLICATIONS

Mini head—phones and electronics.

- A:** Soft Black **PVC** sheath.
Outer Dim. 1,90x4,00 (±0,20) mm.
- B:** The single conductors are shielded with O.F.C. tinned copper spiral covering 100%.
- C:** Core Insulation with PVC, colored one White and one Red.
Diam. Ø 0,90 (±0,20) mm.
- D:** O.F.C. red copper formation 12x0,10 mm
Nom. Cross section 2x0,10 mm².

MARKING

tasker® C117 2x0,10 mm² O.F.C. Shielded Flat Cable

CUSTOM

This product may be custom produced also in **L.S.Z.H.** polymer, **PE** or **PUR**.

PRODUCTION

Cable Properties

Conductor Resistance	203 Ω/Km
Capacity Core/Core	70 pF/m
Capacity Core/Shield	300 pF/m
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. B / 14.03.19
		Outdoor	Esterno			Mobile	Mobile			Formation in accordance with CEI 20-29 and IEC228
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			