

MILAN S.r.l. a socio unico

Head Office – Export department:

Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione

Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet **tasker® TSK50 – 2x0,35 mm²** **Red & Black Flat Audio Divisible Cable**



CATEGORY Flat Cable (See Audio Catalogue)

APPLICATIONS Speaker and Home Theatre installation

A: Red and Black Soft **PVC** Sheath.
 Outer cable dimension 2,00x4,00 (±0,20) mm.

B: Both conductors in CCA - Formation with 0,20 mm wires.
 Nominal cross section 2x0,35 mm².

MARKING Cable not Marked.

CUSTOM PRODUCTION This product may be custom produced also in **L.S.Z.H.** polymer, **PE** or **PUR**.

Cable Properties

Conductor Resistance	60,00 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS3 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. B / 16.05.19
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			