

## Technical Datasheet

### **tasker® TSK53 – 2x1,00 mm<sup>2</sup>**

### Flat Audio Divisible Cable



A

B

**CATEGORY** Flat Cable (See Audio Catalogue)

**APPLICATIONS** Speaker and Home Theatre installation

**A:** Red and Black Soft **PVC** Sheath.  
Outer cable dimension 2,80x5,60 (±0,20) mm.

**B:** Both conductors in CCA - Formation with 0,20 mm wires.  
Nominal cross section 2x1,00 mm<sup>2</sup>.

**MARKING** Cable not Marked

**CUSTOM PRODUCTION** This product may be custom produced also in **L.S.Z.H.** polymer, **PE** or **PUR**.

#### Cable Properties

|                              |            |
|------------------------------|------------|
| <b>Conductor Resistance</b>  | 21,00 Ω/Km |
| <b>Max Rated Voltage</b>     | 49 V       |
| <b>Operative Temperature</b> | -15/+70°C  |

|                |          |                       |                   |
|----------------|----------|-----------------------|-------------------|
| <b>USE</b>     | <b>X</b> | Indoor                | Interno Edificio  |
| <b>Impiego</b> |          | Outdoor Limited       | Esterno Limitato  |
|                |          | Outdoor               | Esterno           |
|                |          | Outdoor Direct Burial | Esterno Interrato |

|                     |          |                      |                  |
|---------------------|----------|----------------------|------------------|
| <b>INSTALLATION</b> | <b>X</b> | Fixed                | Fissa            |
| <b>Posa</b>         | <b>X</b> | Restricted Mobile    | Mobile Limitata  |
|                     |          | Mobile               | Mobile           |
|                     |          | Mobile in Drag Chain | Mobile in Catena |

|                     |          |                   |
|---------------------|----------|-------------------|
| <b>INFORMATION</b>  | <b>X</b> | RoHS3 Compliant   |
| <b>Informazioni</b> | <b>X</b> | Ver. B / 16.05.19 |
|                     |          |                   |