

	1	2	3	4	5	6	7			
						Signature Sean	Revision History For Bulk Production	Date May.20.2013	Rev. 01	
A	RoHS Compliant									A
B	USB A TYPE MALE P1 4 3 2 1 1800±50mm A A ②③ ① ②③ USB B TYPE MALE P2 2 3 1 4									B
C	LQ-01									C
D										D
E	PIN ASSIGNMENT P1 P2 1 2 3 4 RED GREEN WHITE BLACK 1 2 3 4 VCC -DATA +DATA GROUND									E
F	NOTES: 1.CABLE: NO-UL 30AWG(7/0.09BC)*4C+PVC JACKET OD=3.5±015mm JACKET COLOR: BLACK 2.CONNECTOR: P1 : USB A/M, SOLDER, WHITE INSULATION, GOLD FLASH PLATED CONTACTS, NICKEL PLATED SHELL P2 : USB B/M, SOLDER, WHITE INSULATION, GOLD FLASH PLATED CONTACTS, NICKEL PLATED SHELL 3.HOOD: MOLDED TYPE,PVC 45P,COLOR:BLACK 4.ELECTRICLE TEST: (1)100% OPEN SHORT & MIS WIRE TEST. (2)CONTACT RESISTANCE 3 ohm Max . (3)INSULATION RESISTANCE 5M ohm Min . (4)HI-POT TEST:DC 300V/10ms									F
G	Cross Section: Conductor Insulatoin Jacket									G
H	STxxxxx ASSMANN Electronic GmbH Part No. AK-300102-018-S EAN:4016032284789 Title USB A/M - B/M CABLE Scale Unit N/A MM Sheet 1/2									H
	1	2	3	4	5	6	7	80492		

	1	2	3	4	5	6	7																																								
A	Package Details					Signature		Revision History		Date	Rev.																																				
						Sean		For Bulk Production		May.20,2013	01																																				
B	Single Cable					Single Cable																																									
C																																															
D	Inner Packing Unit					Inner Packing Unit																																									
E																																															
F	CARTON DETAILS					Inner Packing Unit																																									
G																																															
H						<table><tr><td></td><td>Date</td><td>Name</td><td colspan="3">Part No.</td></tr><tr><td>Drawn by</td><td>May.20,2013</td><td>Sean</td><td colspan="3">AK-300102-018-S</td></tr><tr><td>Checked by</td><td>May.20,2013</td><td>Joe</td><td colspan="3">EAN:4016032284789</td></tr><tr><td>Approved by</td><td>May.20,2013</td><td>Andy</td><td colspan="3">Title</td></tr><tr><td colspan="3" rowspan="3">ASSMANN Electronic GmbH</td><td colspan="3">USB A/M - B/M CABLE</td></tr><tr><td>Scale</td><td>N/A</td><td>Sheet</td></tr><tr><td>Unit</td><td>MM</td><td>2/2</td></tr></table>							Date	Name	Part No.			Drawn by	May.20,2013	Sean	AK-300102-018-S			Checked by	May.20,2013	Joe	EAN:4016032284789			Approved by	May.20,2013	Andy	Title			ASSMANN Electronic GmbH			USB A/M - B/M CABLE			Scale	N/A	Sheet	Unit	MM	2/2
	Date	Name	Part No.																																												
Drawn by	May.20,2013	Sean	AK-300102-018-S																																												
Checked by	May.20,2013	Joe	EAN:4016032284789																																												
Approved by	May.20,2013	Andy	Title																																												
ASSMANN Electronic GmbH			USB A/M - B/M CABLE																																												
			Scale	N/A	Sheet																																										
			Unit	MM	2/2																																										
* "ROTTERDAM" is for Sea Freight shipment * "COLOGNE" is for Air Freight shipment * "LUDENSCHIED" is for Fedex or UPS shipment					80492																																										