

EF-EMC 20 54 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

General ordering data

Type	EF-EMC 20 54 GY
Order No.	2557570000
Version	Exhaust filter, IP54, grey
GTIN (EAN)	4050118568219
Qty.	1 pc(s).

EF-EMC 20 54 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	145 mm	Width (inches)	5.709 inch
Height	145 mm	Height (inches)	5.709 inch
Depth	31 mm	Depth (inches)	1.22 inch
Net weight	180 g		

General data

Colour	grey	EMC version	EN 61000-3-2,-3, EN 61000-6-2, 3
Filter class	G 4	Height of installation cut-outs	126.5 mm
Material	Thermoplastic	Mounting depth	26 mm
Mounting height	5 mm	Operating temperature range	-40...55 °C
Protection class (UL)	Type 12	Type of mounting	Snap-on
Width of installation cut-outs	126.5 mm	With filter	Yes

Classifications

ETIM 6.0	EC002513	ETIM 7.0	EC002513
eClass 9.1	27-18-07-06	eClass 10.0	27-18-07-06

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
User Documentation	Installation- and operating instructions

EF-EMC 20 54 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Graph

Shielding effectiveness measurements

