

**EF 20 54 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | EF 20 54 GY                |
| Order No.  | <a href="#">2557090000</a> |
| Version    | Exhaust filter, IP54, grey |
| GTIN (EAN) | 4050118567724              |
| Qty.       | 1 pc(s).                   |

**EF 20 54 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Width      | 145 mm | Width (inches)  | 5.709 inch |
| Height     | 145 mm | Height (inches) | 5.709 inch |
| Depth      | 31 mm  | Depth (inches)  | 1.22 inch  |
| Net weight | 120 g  |                 |            |

**General data**

|                                |               |                                 |             |
|--------------------------------|---------------|---------------------------------|-------------|
| Colour                         | grey          | EMC version                     | No          |
| Filter class                   | G 4           | Height of installation cut-outs | 125 mm      |
| Material                       | Thermoplastic | Mounting depth                  | 26 mm       |
| Mounting height                | 5 mm          | Operating temperature range     | -40...55 °C |
| Protection class (UL)          | Type 12       | Type of mounting                | Snap-on     |
| Width of installation cut-outs | 125 mm        | With filter                     | Yes         |

**Classifications**

|            |             |             |             |
|------------|-------------|-------------|-------------|
| ETIM 6.0   | EC002513    | ETIM 7.0    | EC002513    |
| eClass 9.1 | 27-18-07-06 | eClass 10.0 | 27-18-07-06 |

**Approvals**

Approvals



ROHS Conform

**Downloads**

|                    |                                                          |
|--------------------|----------------------------------------------------------|
| Engineering Data   | <a href="#">STEP</a>                                     |
| User Documentation | <a href="#">Installation- and operating instructions</a> |