

EF 60 54 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

General ordering data

Type	EF 60 54 BK
Order No.	2557220000
Version	Exhaust filter, IP54, black
GTIN (EAN)	4050118567854
Qty.	1 pc(s).

EF 60 54 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	320 mm	Width (inches)	12.598 inch
Height	320 mm	Height (inches)	12.598 inch
Depth	46 mm	Depth (inches)	1.811 inch
Net weight	700 g		

General data

Colour	black	EMC version	No
Filter class	G 3	Height of installation cut-outs	291 mm
Material	Thermoplastic	Mounting depth	39 mm
Mounting height	7 mm	Operating temperature range	-40...55 °C
Protection class (UL)	Type 12	Type of mounting	Snap-on
Width of installation cut-outs	291 mm	With filter	Yes

Classifications

ETIM 6.0	EC002513	ETIM 7.0	EC002513
eClass 9.1	27-18-07-06	eClass 10.0	27-18-07-06

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	STEP
User Documentation	Installation- and operating instructions