

FF-FIMT 3X 54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

General ordering data

Type	FF-FIMT 3X 54
Order No.	2556720000
Version	Filter mat, IP54, white
GTIN (EAN)	4050118567342
Qty.	5 pc(s).

FF-FIMT 3X 54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	170 mm	Width (inches)	6.693 inch
Height	170 mm	Height (inches)	6.693 inch
Net weight	9.6 g		

General data

Colour	white	Filter class	G 4
Operating temperature range	-40...55 °C	Protection class (UL)	Type 12
Type of mounting	Snap-on	With filter	Yes

Classifications

ETIM 6.0	EC002513	ETIM 7.0	EC002513
eClass 9.1	27-18-07-06	eClass 10.0	27-18-07-06

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	Operating instructions
--------------------	--